# VPM-5 SmartPirani<sup>™</sup> vacuum transducer

Heat-loss Pirani and diaphragm Piezo combination gauge with 1.0E-6 to 1333 mbar measuring range



#### **Benefits & features**

- Ultra-wide measuring range of 9 decades from 1.0E-6 to 1333 mbar
- Unmatched price-performance ratio
- Gas independent measurement from 2 to 1333 mbar
- Easy configuration with USB programmer
- 0-10 VDC programmable voltage output
- Digital RS-232 or RS-485 interface
- Optional Ceramic or Parylene sensor protection for corrosive applications
- Optional solid state setpoint relay for external controlling
- Pin and output compatibility with other vendors' gauges



### **Typical applications**

- Analytical instrumentation
- Semiconductor processing
- Vacuum furnaces
- Thin film coating
- Medical instrumentation
- Space simulation and flight

Product datasheet






## Leading technology

The VPM-5 SmartPirani<sup>™</sup> transducer offers best-in-class performance and has established new standards for vacuum measurement by extending the useable measuring range for thermal conductivity vacuum gauges by 1-3 decades.

The SmartPirani<sup>™</sup> is based on cutting edge MEMS (Microelectromechanical Systems) sensor technology, combined with a novel precision digital signal processing architecture and advanced innovative measurement algorithms. Together with precision automated manufacturing and calibration processes, these elements in combination provide a unique product capable of uncompromised measurement performance.



Vacuum pressure in mbar

The well-known gas dependency in the rough vacuum range of thermal conductivity gauges has been eliminated by integrating a MEMS diaphragm sensor that offers precision performance comparable to more expensive capacitance manometers. The measurement is independent of gas type and concentration which enhances confidence in the measurement and ensures more accurate control of vacuum system venting processes and can prevent over-pressurization of the vacuum system.

## **Enabling use in demanding applications**

For applications where the sensors can be exposed to corrosive or aggressive gases, the SmartPirani<sup>™</sup> is available with conformal protective coating that acts as an efficient barrier.

Depending on the application the SmartPirani<sup>™</sup> transducer series is now available with either an optional ceramic or Parylene protective barrier against corrosion or oxidation of sensor materials.

Ceramic is highly corrosion resistant and is a well-proven material for vacuum sensor diaphragms in capacitance diaphragm gauges.

Parylene is a unique polymer with highly corrosion resistant and hydrophobic properties. The Parylene barrier is designed for medical applications including lyophilization and sterilization.

In some vacuum processes, particulates can damage vacuum gauges and for these applications the SmartPirani<sup>™</sup> transducers are offered with a protective baffle that acts as a barrier for macroscopic particles.

In combination with the protective coating options the new SmartPirani<sup>™</sup> transducers are set for tough vacuum environments.






## Measure and control advanced vacuum processes

The VPM-5 SmartPirani<sup>™</sup> is engineered for best-in-class measurement and control of vacuum gas pressure. Several output options are providing more than just a pressure measurement signal.

### Analog voltage output

The analog output voltage provides a signal for external readout or controls. The VPM-5 offers as standard a voltage output signal of 1VDC/decade mbar, Torr, or Pascal. Furthermore, it can also be user configured or ordered preconfigured with a large selection of other analog output options that enables drop-in replacement of gauges from other vendors.



## **Digital interface**

The RS-232 and RS-485 serial interface can be used to transfer pressure and temperature measurement data to external equipment.

The digital interface enables diagnostics, predictive maintenance, service, calibration, setpoint configuration, analog output scaling and acquisition of real-time vacuum pressure measurements for on-screen visualization.

## Reliable and robust setpoint relay control

The three independent solid-state switch relays can be used for external control of pumps, valves, safety interlock circuits and other external equipment. The basic control uses on/off regulation with a programmable setpoint and hysteresis value. Each solid-state relay offers both normally closed and normally open contacts.

Compared to electro-mechanical relays, the solid-state relays offer superior reliability and faster switching time while providing arc free contacts and generating no EMI (electromagnetic interference) when switching contacts.

The SmartPirani<sup>™</sup> relays are designed to last and are UL listed, CSA recognized, and EN/IEC 60950-1 certified for maximum confidence when used to control critical vacuum processes and high-cycle applications.

## **Temperature measurement**

The VPM-5 SmartPirani<sup>™</sup> is designed for measuring pressure, but also offers vacuum side temperature measurement signal that can be used for vacuum process surveillance and diagnostic. The temperature measurement can be accessed through the digital interface.

## **Customized settings**

The VPM-5 transducer can be delivered with a custom configuration to match specific application requirements and work for a specific equipment installation out of the box. Examples of pre-configured options include measurement range, vacuum pressure unit, setpoint configuration, and output signal scaling.

Customized products will be assigned a unique part number for easy and simple future reordering.



## Other vendor compatibility

The VPM-5 SmartPirani<sup>™</sup> transducer is available with pin compatibility, analog voltage pressure signal emulation and digital protocol emulation with vacuum transducers and transmitters from other vendors. The other vendor emulation features enable quick, seamless upgrading of traditional wire Pirani transducers, convection gauges and legacy micro-Pirani transducers and allows moving to next-generation vacuum transducers without change of cabling and system equipment software.

The VPM-5 SmartPirani<sup>™</sup> will in many applications provide both cost reduction and enhanced measurement performance when replacing legacy vacuum gauges and transducers.

The other vendor emulation also provides compatibility with other vendors controller and display units.



#### Connect digital through supply voltage line

Traditionally other vendors transducers equipped with FCC68/RJ45/8P8C and Hirschman connector do not offer digital communication. The novel S4-connect interface enables access to the digital core of the VPM-5 transducer though digital communication over the power supply line.


The S4-Connect USB communicator enables easy configuration of transducer settings, diagnostic and adjustment of calibration.

## **Datalogging and analyzing**

The SmartPirani<sup>™</sup> Communicator user software is freeware software package for Windows that offers real time onscreen measurements and a comprehensive data-logger tool for logging measurement data to a file for storing, data analysis or presentation.

The SmartPirani<sup>™</sup> Communicator is a freeware software compatible with the SmartPirani<sup>™</sup> transducer series with RS-232 and RS-485 digital interface.

The SmartPirani<sup>™</sup> transducer in combination with the power supply and USB converter is a costeffective data-logger package for characterization of vacuum system performance and rate-of-rise leak detection.





The SmartPirani<sup>™</sup> is designed for reliable measurement and control of advanced vacuum processes and suitable for a wide range of applications in industry and science. The wide selection of VPM-5 configurations is available to meet different requirements in various applications.

### **Analytical instrumentation**

Mass spectrometers and scanning electron microscopes are types of analytical equipment that use vacuum gauges to determine safe operation of an ion source. In certain applications, the ultra-wide range of the SmartPirani<sup>™</sup> eliminates the need for additional expensive high vacuum ionization gauges.



**AISENIS** 



### Semiconductor industry

Traditionally, convection type wire Pirani vacuum gauges has been used in the semiconductor industry, because of their resistance to corrosive gases.

The new protective Ceramic or Parylene sensor surface option expands the applicable applications for the MEMS Pirani based vacuum transducers and is now a real performance upgrade alternative to legacy convection vacuum gauges.

## Physical vapor deposition

Coating of materials by use of physical vapor deposition (PVD) processes is used in many diverse industries including solar, medical, automotive, tooling, optics and packaging. The SmartPirani<sup>™</sup> is available with a user-cleanable integrated particulate baffle system specially designed for PVD applications. The baffle system is designed for blocking particulates while ensuring sufficiently high vacuum gas conductance and preventing clogging of particulates. The innovative baffle feature can increase time between service intervals and increase equipment up-time. Furthermore, in certain PVD applications the extended range of the SmartPirani<sup>™</sup> eliminates the need for cold cathode vacuum gauges for base pressure verification.





# **Technical data**

Specifications Specifications	
Measuring range in mbar	1×10 <sup>-6</sup> to 1333 mbar (7.5×10 <sup>-7</sup> to 1000 Torr)
Measuring principle 1×10 <sup>-6</sup> to 1.5 mbar	MEMS Pirani thermal conductivity
Measuring principle 1.5 to 2 mbar	Blended MEMS Pirani / piezo reading
Measuring principle 2 to 1333 mbar	MEMS piezo resistive diaphragm
Accuracy 1×10 <sup>-5</sup> to 9.99×10 <sup>-5</sup>	25% of reading
Accuracy 1×10 <sup>-4</sup> to 7.99 mbar	5% of reading
Accuracy 8.00 to 99.9 mbar	1% of reading
Accuracy 100 to 800 mbar	0.5% of reading
Accuracy 800 to 1099 mbar	0.25% of reading
Accuracy 1100 to 1333 mbar	0.5% reading
Hysteresis 1×10 <sup>-3</sup> to 10 mbar (ISO19685:2017)	1%
Hysteresis 10 to 1333 mbar (ISO19685:2017)	0.1%
Analog output resolution	16 bit (150 μV)
Analog output update rate	124 Hz
Response time (ISO 19685:2017)	<20 ms
Temperature compensation	+10 to +50 °C
Solid state relay set point range	5×10 <sup>-6</sup> to 1333 mbar (3.75×10 <sup>-6</sup> to 1000 Torr)
Solid state relay contact rating	50 V, 100 mA <sub>rms</sub> / mA <sub>DC</sub>
Solid state relay approvals	UL Recognized: File E76270
	CSA Certified: Certificate 1175739
	EN/IEC 60950-1 Certified
Environment conditions invironment conditions	
Operating ambient temperature	-20 to +50 °C
Media temperature	-20 to +50 °C
Storage ambient temperature	-40 to +120 °C
Bake-out temperature (non-operating)	+120 °C
Maximum media pressure <sup>(3)</sup>	10 bar absolute
Mounting position	Arbitrary
Protection rating, EN 60529/A2:2013	IP40
Humidity, IEC 68-2-38	98%, non-condensing
Power supply Power supply	
Supply voltage	12-30 VDC
Power consumption	240 mW (max)
Reverse polarity protection	Yes
Overvoltage protection	Yes
Internal fuse	100 mA (thermal recoverable)
Materials aterials	
Enclosure	SS 1.4307 / AISI 304L / Aluminum 6061
Vacuum Process flange (media wetted)	SS 1.4401 / AISI 316
Vacuum exposed materials (media wetted)	316 Stainless steel, Kovar, glass, silicon, nicke
Standard version	aluminum, SiO <sub>2</sub> , Si <sub>3</sub> N <sub>4</sub> , gold, Viton <sup>®</sup> , low out-gassin
	epoxy resin, solder, RO4305
Vacuum exposed materials (media wetted)	316 Stainless steel, Viton <sup>®</sup> , Parylene
Parylene protected version	
Vacuum exposed materials (media wetted)	316 Stainless steel, Viton <sup>®</sup> , Aluminum oxide cerami
Ceramic protected version	(Al <sub>2</sub> O <sub>3</sub> )
Process leak tightness	<1·10 <sup>-9</sup> mbar·l/s
Approvals provals	
CE	EMC directive 2014/30/EU
RoHS compliance	Directive EU 2015/863

(2) Viton<sup>®</sup> is a trademark of THE CHEMOURS COMPANY FC, LLC


(3) Overpressure limits only applicable with using fittings rated to the specified

Specifications are subject to change without further notice.

# **Connector Pin outs**

#### 15 Pin HD D-sub RS-232 / RS-485

Pin	Description
1	RS-232 Transmit / RS-485 (-)
2	RS-232 Receive / RS-485 (+)
3	Supply voltage 12-30 VDC
4	Supply voltage – (return)
5	Analog voltage signal +
6	Analog voltage signal – (return)
7	Relay 1 NO (normally open contact) $^{(4)}$
8	Relay 1 Common <sup>(1)</sup>
9	Relay 1 NC (normally closed contact) <sup>(4)</sup>
10	Relay 2 NC (normally closed contact) <sup>(4)</sup>
11	Relay 2 Common <sup>(1)</sup>
12	Relay 2 NO (normally open contact) <sup>(4)</sup>
13	Relay 3 NO (normally open contact) $^{(4)}$ or analog out 2 $^{(5)}$
14	Relay 3 Common <sup>(1)</sup>
15	Relay 3 NO (normally open contact) <sup>(4)</sup>
(4)	Optional relay
(5)	Optional secondary analog voltage output



**«SENS**<sup>4</sup>

#### 9 Pin D-sub RS-232 / RS-485

Pin	Description
1	Relay 1 NO (normally open contact) <sup>(6)</sup>
2	Relay 1 NC (normally closed contact) <sup>(6)</sup>
3	Supply voltage 12-30 VDC
4	Supply voltage – (return)
5	Analog voltage signal +
6	Relay 1 Common <sup>(6)</sup>
7	RS-232 Transmit / RS-485 (-)
8	Analog voltage signal – (return)
9	RS-232 Receive / RS-485 (+)
	(6) Optional relay


#### 6 Pin Hirschmann connector


Pin	Description
1	Identification resistor (3K)
2	Analog voltage signal +
3	Analog voltage signal – (return)
4	Supply voltage 12-30 VDC
5	Supply voltage – (return)
6	Chassis


### 8 Pin RJ45 / 8P8C

Pin	Description
1	Supply voltage 12-30 VDC
2	Supply voltage – (return)
3	Analog pressure voltage signal +
4	Identification resistor
5	Analog pressure voltage signal – (return)
6	Relay 2 NO (normally open contact) <sup>(7)</sup>
7	Relay 1 NO (normally open contact) <sup>(7)</sup>
8	Relay COMMON <sup>(7)</sup>
1.	7) Ontional ralay

(7) Optional relay










# Dimensions



Flange type	A [mm]	B [mm]	A [inch.]	B [inch.]
DN16KF (P/N: VPM-5-1)	12.00	40.00	0.47	1.57
DN25KF (P/N: VPM-5-2)	12.00	40.00	0.47	1.57
VCR4 <sup>1</sup> (P/N: VPM-5-4)	33.70	61.70	1.32	2.43
VCR8 <sup>1</sup> (P/N: VPM-5-5)	29.43	57.43	1.15	2.26
1/8" NPT (P/N: VPM-5-3)	37.00	65.00	1.45	2.56
DN16CF (P/N: VPM-5-6)	21.83	49.83	0.86	1.96

DN16KF flange / D-SUB Connector	DN25KF flange / D-SUB Connector	VCR4F flange / D-SUB Connector	VCR8F flange / D-SUB Connector
1/8" NPT flange / D-SUB Connector	DN16CF flange / D-SUB Connector	DN16KF Extended flange / D-SUB Connector	DN16KF flange / FCC68 Connector
DN16KF Extended flange / FCC68 Connector	VCR4F flange / FCC68 Connector	DN16KF flange / Hirschmann Connector	DN16KF flange / Hirschmann Connector



Datasheet

# Order guide

<b>acuum flange / sensor p</b> DN16KF							' I	Connecti
	rotection							1 9 Pin D-sub ma
		i	0					2 15 pin HD D-sub ma
DN25KF		2	0					3 15 pin HD D-Sub male / dual analog of
NPT 1/8"		3	0					4 6 pin Hirschmann, ID res 3
/CR4 female		4	0					5 6 pin Hirschmann, ID res 5.1
DN16KF Extended		8	0					6 6 pin Hirschmann, ID res 9.1K/11.1
0N16KF with light baffle		1	1					7 8 pin RJ45 / FCC68, ID Res 27
DN16KF with heavy duty l		1	2					8 8 pin RJ45 / FCC68, ID Res 36
N25KF with light baffle		2 2	1 2					9 8 pin RJ45 / FCC68, ID Res 43 A 8 pin RJ45 / FCC68, ID Res 71 K
DN25KF with heavy duty l DN16KF, Ceramic protect		2	3					A 8 pin RJ45 / FCC68, ID Res 71k
N25KF, Ceramic protect		2	3					Setpoints
NPT 1/8", Ceramic protect		3	3				0	None
/CR4 female, Ceramic pro		4	3				1	1x Solid-State Relay (Only 9 pin D-sub)
/CR8 female, Ceramic pro		5	3				2	2x Solid State Relays (Only RJ45/FCC68)
0N16CF rotateble, Ceram		6	3				3	3x Solid State Relays (Only 15 pin HD D-sub)
N16KF Extended, Ceram	nic	8	3					
ON16KF with light baffle,	Ceramic	1	4					Unit
DN16KF with heavy duty l		1	5			i		torr
N25KF with light baffle,		1	4			2		mbar
DN16KF, Parylene protec		1	6			3		Pascal
N25KF, Parylene protec		2	6					
NPT 1/8", Parylene protec		3	6					
/CR4 female, Parylene pr		4 5	6 6					
/CR8 female, Parylene pr DN16CF rotateble Paryler		5 6	6					
0N16KF Extended, Paryle	•	8	6					
DN16KF with light baffle,		1	7					
0N16KF with heavy duty l		1	8					
N25KF with light baffle,		2	7					
N25KF with heavy duty l	baffle, Parylene	2	8					
	/ S4-Connect <sup>™</sup> (9 and 15 pi			2				
S4-Conn	ect™ (RJ45/FCC68 and Hir			3				
	ect <sup>™</sup> (RJ45/FCC68 and Hir Analog Output			3				
	ect <sup>™</sup> (RJ45/FCC68 and Hir Analog Output 0.5 - 9.5 (1 V/dec)	schmann)	. :	3 0	1			
	ect <sup>™</sup> (RJ45/FCC68 and Hir Analog Output 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH	schmann) (S 901P/9	. :	3 0 0	2			
	ect <sup>™</sup> (RJ45/FCC68 and Hir Analog Output 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS	schmann) (S 901P/9	. :	3 0 0 0	2 3			
	ect <sup>™</sup> (RJ45/FCC68 and Hir Analog Output 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523)	schmann) (S 901P/9 GP275)	25/910)	3 0 0 0 0	2 3 4			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PS65	schmann) (S 901P/9 GP275) (5x, Leybol	25/910) Id TTR91)	3 0 0 0 0 0 0	2 3 4 5			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PS65 1.5-8.5 VDC (Pfeiffer TPR	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2	25/910) Id TTR91)	3 0 0 0 0 0 0 0	2 3 4 5 6			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 V/dec) 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APC	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC)	25/910) Id TTR91)	3 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7			
	ect <sup>™</sup> (RJ45/FCC68 and Hir <b>Analog Output</b> 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PS65 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APC 1.9-9.1VDC (Edwards APC	schmann) (S 901P/9 GP275) 5x, Leybol 260/27x/2 G100XLC) G100XM)	25/910) Id TTR91)	3 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8			
	ect <sup>™</sup> (RJ45/FCC68 and Hir Analog Output 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG-L 2-10VDC (Edwards APG-L	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC) G100XM) .)	25/910) Id TTR91) 28x)	3 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG- 1.9-9.1VDC (Edwards APG- 2-10VDC (Edwards APG- 0-10 VDC 0.1Torr FS Capa	schmann) (S 901P/9 (GP275) (5x, Leybol 260/27x/2 G100XLC) G100XM) .) Incitance m	25/910) Id TTR91) 28x) nanometer	3 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG- 1.9-9.1VDC (Edwards APG- 0-10 VDC (Edwards APG- 0-10 VDC 0.1Torr FS Capa 0-10 VDC 1 Torr FS Capa	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 3100XLC) 3100XM) () nottance maitance maitanc	25/910) Id TTR91) 28x) nanometer anometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APC 2.10VDC (Edwards APG-L 0-10 VDC 0.1Torr FS Capa 0-10 VDC 1 Torr FS Capa 0-10 VDC 10 Torr FS Capa	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC) G100XLC) G100XLC) (Comparison (Comparison) (Comparis	25/910) Id TTR91) 28x) nanometer nanometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2			
	ect <sup>™</sup> (RJ45/FCC68 and Hir <b>Analog Output</b> 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APC 2-10VDC (Edwards APC 2-10VDC (Edwards APC 0-10 VDC 0.1 Torr FS Capac 0-10 VDC 10 Torr FS Capac 0-10 VDC 10 Torr FS Capac	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC) G100XM) () icitance ma icitance ma icitance ma	25/910) Id TTR91) 28x) nanometer nometer nometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APC 2.10VDC (Edwards APG-L 0-10 VDC 0.1Torr FS Capa 0-10 VDC 1 Torr FS Capa 0-10 VDC 10 Torr FS Capa	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC) G100XLC]	25/910) Id TTR91) 28x) nanometer nanometer anometer anometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2 3			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APC 2-10VDC (Edwards APG-L 0-10 VDC 1.Torr FS Capa 0-10 VDC 10 Torr FS Capa 0-10 VDC 10 Torr FS Capa 0-10 VDC 100 Torr Capaci 0-10 VDC 100 Torr Capaci 0-10 VDC 1000 Torr Capaci	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC)	25/910) Id TTR91) 28x) nanometer nanometer anometer anometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 1 2 3 4			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG-L 0.9-0.1VDC (Edwards APG-L 0-10 VDC 10Torr FS Capac 0-10 VDC 1 Torr FS Capac 0-10 VDC 100 Torr Capaci 0-10 VDC 100 Torr Capaci	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC) G100XLC) G100XLC) G100XLC) G100XLC) G100XLC) G100XLC) (G100XLC) (G100XLC) (G100XLC) (G10XL	25/910) Id TTR91) 28x) nanometer nanometer anometer anometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 1 2 3 4 5			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PS65 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG-1 0.9-1) VDC (Edwards APG-1 0-10 VDC (Inter FS Capac 0-10 VDC 1 Torr FS Capac 0-10 VDC 10 Torr FS Capac 0-10 VDC 10 Torr Capaci 0-10 VDC 100 Torr Capaci 0-10 VDC 100 Torr Capaci 0-10 VDC 1000 Torr	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 3100XLC)	25/910) Id TTR91) 28x) nanometer anometer nometer anometer anometer 251, PKR2	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2 3 4 5 5			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG-L 0-10 VDC (1Torr FS Capa 0-10 VDC (1 Torr FS Capa 0-10 VDC 10 Torr FS Capa 0-10 VDC 10 Torr FS Capa 0-10 VDC 100 Torr Capaci 0-10 VDC 100 Torr Capaci 0-10 VDC 1000 Torr	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 3100XLC) 3100XLC) (3100XLC)	25/910) Id TTR91) 28x) nanometer nometer anometer anometer 251, PKR2 manomete	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2 3 4 5 5 5 6			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.57 DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1 VDC (Edwards APG-L 0-10 VDC (Edwards APG-L 0-10 VDC (Edwards APG-L 0-10 VDC (Edwards APG-L 0-10 VDC 1 Torr FS Capa 0-10 VDC 10 Torr FS Capa 0-10 VDC 100 Torr Capaci 0-10	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC) G100XLC) G100XLC) (3100XLC) (	25/910) Id TTR91) 28x) nanometer nanometer anometer anometer 251, PKR2 manomete anometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2 3 4 5 5 5 6 0			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG-L 0-10 VDC (Dewards APG-L 0-10 VDC (Edwards APG-L 0-10 VDC 10 Torr FS Capa 0-10 VDC 10 Torr FS Capa 0-10 VDC 100 Torr Capaci 0-10 VDC 100 Torr FS Capa 0-10 VDC 100 Torr FS Capa 0-10 VDC 0.1 mbar FS Capa 0-10 VDC 1 mbar FS Capa	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 3100XLC) 3100XLC) 3100XLC) 3100XM) (citance ma citance ma citance ma citance ma citance ma citance ma citance ma citance ma citance ma	25/910) Id TTR91) 28x) nanometer nanometer anometer 251, PKR2 manomete anometer anometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2 3 4 5 5 6 0 1			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG-L 0-10 VDC 100 Torr FS Capac 0-10 VDC 1 Torr FS Capac 0-10 VDC 100 Torr Capaci 0-10 VDC 0.1 mbar FS Capa 0-10 VDC 1 mbar FS Capaci 0-10 VDC 1 mbar FS Capaci	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC)	25/910) Id TTR91) 28x) nanometer anometer anometer 251, PKR2 manometer anometer anometer anometer anometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 1 2 3 4 5 5 6 0 0 1 2			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG-L 0.10 VDC (Edwards APG-L 0.10 VDC (Edwards APG-L 0.10 VDC (Edwards APG-L 0.10 VDC (Information Scapac) 0.10 VDC 100r TPS Capac 0.10 VDC 100r TPS Capac 0.10 VDC 100r Torr Capaci 0.10 VDC 1000 Torr SC Capac 0.10 VDC 1000 Torr SC Capac 0.10 VDC 0.11 Mbar FS Capac 0.10 VDC 0.11 Mbar FS Capac 0.10 VDC 2 mbar FS Capac 0.10 VDC 2 mbar FS Capac	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC)	25/910) Id TTR91) 28x) nanometer anometer anometer anometer anometer anometer anometer anometer anometer anometer anometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2 3 4 5 5 5 6 0 1 2 3 3			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG-L 0-10 VDC (Edwards APG-L 0-10 VDC (Edwards APG-L 0-10 VDC 10 Torr FS Capa 0-10 VDC 10 Torr Capaci 0-10 VDC 10 Torr Capaci 0-10 VDC 10 Torr FS Capa 0-10 VDC 10 Torr FS Capa 0-10 VDC 10 Torr FS Capa 0-10 VDC 10 Torr FS Capa 0-10VDC 0.1 mbar FS Capa 0-10VDC 1 mbar FS Capa 0-10VDC 2 mbar FS Capa 0-10VDC 2 mbar FS Capa 0-10VDC 20 mbar FS Capa 0-10VDC 20 mbar FS Capa 0-10VDC 20 mbar FS Capa 0-10VDC 20 mbar FS Capa	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC) G100XLC) G100XLC) G100XLC) G100XM) (citance m itance ma citance ma citance ma citance ma citance ma citance ma citance ma citance ma	25/910) Id TTR91) 28x) nanometer anometer anometer anometer anometer anometer anometer nanometer nanometer nanometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2 3 4 5 5 6 0 1 2 3 4 5 5 6 0			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Feirffer TPR 1.9-9.1VDC (Edwards APG-L 0-10 VDC (Information PSG) 2-10VDC (Edwards APG-L 0-10 VDC (Information PSG) 0-10 VDC 10 Torr FS Capa 0-10 VDC 100 Torr Capaci 0-10 VDC 100 Torr Capaci 0-10 VDC 100 Torr Capaci 0-10 VDC (Information PSG) 0-10 VDC (Information PSG) 0-10 VDC 0.1 mbar FS Capaci 0-10 VDC 10	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC) G100XLC) G100XLC) G100XLC) G100XM) (citance m itance ma citance ma citance ma citance ma citance ma citance ma citance ma citance ma	25/910) Id TTR91) 28x) nanometer anometer anometer anometer anometer anometer anometer nanometer nanometer nanometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2 3 4 5 5 6 0 1 1 2 3 4 5 5			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG-L 0.10 VDC (Edwards APG-L 0.10 VDC (Edwards APG-L 0.10 VDC (Edwards APG-L 0.10 VDC (Infired SAPG-L 0.10 VDC 10 Torr FS Capac 0-10 VDC 100 Torr Capaci 0-10 VDC 100 Torr S Capac 0-10 VDC 100 Torr S Capac 0-10 VDC 100 Torr S Capac 0-10 VDC 0.1 mbar FS Capac 0-10 VDC 0.1 mbar FS Capac 0-10 VDC 10 mbar FS Capac 0-10 VDC 100 mbar FS Capac 0-	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC)	25/910) Id TTR91) 28x) hanometer anometer anometer anometer anometer anometer anometer anometer nanometer manometer manometer manometer manometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2 3 4 5 5 6 0 1 2 3 4 5 5 6 0 1 2 3 4 5 5 6 7 8			
	ect <sup>™</sup> (RJ45/FCC68 and Hir 0.5 - 9.5 (1 V/dec) 1.0-9 VDC 1 VDC/Dec (MH 0.375 to 5.659 VDC (MKS 0.5V DC (MKS 523) 1.9-10 VDC (Inficon PSG5 1.5-8.5 VDC (Pfeiffer TPR 1.9-9.1VDC (Edwards APG-L 0-10 VDC (Edwards APG-L 0-10 VDC (Edwards APG-L 0-10 VDC 10Torr FS Capa 0-10 VDC 100 Torr Capaci 0-10 VDC 100 Torr SC Capaci 0-10 VDC 0.1 mbar FS Capaci 0-10 VDC 2 mbar FS Capaci 0-10 VDC 50 mbar FS Capaci 0-10 VDC 50 mbar FS Capaci 0-10 VDC 100 mbar FS Capaci 0-10 VDC 50 mbar FS Capaci 0-10 VDC 50 mbar FS Capaci 0-10 VDC 100 mbar FS Capaci 0-10 VDC 100 mbar FS Capaci 0-10 VDC 50 mbar FS Capaci 0-10 VDC 50 mbar FS Capaci 0-10 VDC 100 mbar FS Capaci 0-10 VDC 50 mbar FS Capa	schmann) (S 901P/9 GP275) (5x, Leybol 260/27x/2 G100XLC)	25/910) Id TTR91) 28x) nanometer anometer nometer anometer anometer anometer anometer nanometer manometer manometer manometer manometer manometer	3 0 0 0 0 0 0 0 0 0 0 0 0 0	2 3 4 5 6 7 8 9 0 1 2 3 4 5 5 6 0 1 1 2 3 4 5 5 6 7			

### Accessories

RS232 / RS485 to USB converter with wall plug power supply

USB-to-Serial converter for VPM-5 SmartPirani transducers with wall plug power supply.


Part number	Description	
PRG-WPRS2-15DS-01	RS-232 to USB, 15 pin HD D-sub, Power supply (90-230VAC)	
PRG-WPRS4-15DS-01	RS-485 to USB, 15 pin HD D-sub, Power supply (90-230VAC)	
PRG-WPRS2-9DS-01	RS-232 to USB, 9 pin D-sub, Power supply (90-230VAC)	
PRG-WPRS4-9DS-01	RS-485 communicator USB, 9 pin D-sub, Power supply (90-230VAC)	· 🖉 🚛



# .

# Other vacuum measurement products

The Sens4 vacuum transducer product range offers the market's most advanced multi-sensor transducers for use in a wide selection of industrial and scientific vacuum applications.



# VPM-15 TriCAP<sup>™</sup> transducer

The VPM-15 TriCAP<sup>™</sup> transducer is pin and output compatible with the VPM-5. The VPM-15 has an additional CDG (Capacitance Diaphragm Gauge) sensor to provide the gas independent measuring from 5.0E-3 to 1333 mbar that can be an advantage in applications where gas composition or type can change.

For demanding applications, the VPM-15 TriCAP<sup>™</sup> is available with corrosion resistant ceramic or Parylene coated sensors.



**ASENS** 

# About

Sens4 is a Danish technology company that develops, manufactures, markets, and distributes vacuum, pressure and temperature measuring equipment for industrial and scientific applications worldwide. It's our mission to provide compelling product solutions that fit our customers' needs and enable them to efficiently measure and control advanced processes around the world.

Learn more about Sens4 on: sens4.com

# **Connect on social media**









#### Contact

Sens4 A/S Nordre Strandvej 119G 3150 Hellebaek Denmark

Phone: +45 88447044 Email: info@sens4.com